

851/1 BTH bits, PH 3 x 25 mm

Bits for Phillips Screws



EAN:	4013288034267	Size:	25x7x7 mm
Part number:	05056414001	Weight:	5 g
Article number:	851/1 BTH PH	Country of origin:	CZ
		Customs tariff number:	82079030

- For Phillips screws
- BiTorsion zone to absorb peak loads
- Considerable reduction in the risk of breakage, significant increase in service life
- Particularly hard for semi-hard materials
- 1/4" hexagon drive (Wera connecting series 1)
- "Take it easy" tool finder: colour coding according to profile and size

High quality bits for Phillips screws with Torsion zone where kinetic energy is diverted from peak loads. This greatly extends the product service life. Extra-hard design, 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_phillips_screws_851_1_bth_ph.html

Wera - 851/1 BTH PH
05056414001 - 4013288034267

Wera Werkzeuge GmbH
Korzeter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for Phillips Screws

BiTorsion Bits




Peak forces that occur in power tool applications often result in premature wear of bits or damage to the screw head. This usually occurs during initial power-up and the when the screw comes to a standstill. Screwdriving could become more productive and safer if these peak loads could be minimised. The Wera BiTorsion system prevents premature wear. The service life of the tool is extended and the productivity of power tool applications significantly increased.

Two cushioning torsion zones




The effectiveness of the BiTorsion system comes from a combination of two shock-absorbing spring elements. Both, bits as well as holders have a cushioning torsion zone that diverts the kinetic energy away from the drive tip during peak loads.

BiTorsion phase 1




The torsion spring integrated into the unique BiTorsion holder absorbs lower levels of peak loads (Phase 1). Any overloading of this spring is effectively prevented by means of a supporting mechanism.

BiTorsion phase 2



Higher peak loads are minimised through the torsion effect of the bit shaft (Phase 2).

Above-average service life



Even the service life of conventional bits is enhanced with the use of the BiTorsion holder and the BiTorsion bit also functions in a normal holder.

Prevents premature wear




The optimally coordinated features of the torsion zones on the bit and holder permit a phased yield when under strain. The two-phase system prevents premature wear. Moreover, a long tool service life is also ensured by the hardness of the bits that matches the respective application.

BiTorsion and conventional tools



The BiTorsion holder and the BiTorsion bit can, of course, be used independently of one another.

"Take it easy" tool finder



"Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_phillips_screws_851_1_bth_ph.html

Wera - 851/1 BTH PH
05056414001 - 4013288034267

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:



mm



inch

		mm	inch
05056410001	PH 1	25	1"
05056412001	PH 2	25	1"
05056414001	PH 3	25	1"

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_the_range_of_bits_bits_for_phillips_screws_851_1_bth_ph.html

Wera - 851/1 BTH PH

05056414001 - 4013288034267

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de