



<b>EAN:</b>	4013288041272	<b>Size:</b>	50x7x6 mm
<b>Part number:</b>	05060147001	<b>Weight:</b>	10 g
<b>Article number:</b>	868/4 BTZ Square-Plus	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- Suitable for square head socket screws
- BiTorsion zone to absorb peak loads
- Considerable reduction in the risk of breakage, significant increase in service life
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

BiTorsion bits for square head socket screws with torsion zone into which kinetic energy is dissipated during peak loads. This significantly increases the product life. Best possible service life with the matching holder. Tough, for universal use. 1/4" hexagonal, suitable for holding tools as per DIN ISO 1173-F 6.3.

**Web link**

<https://www.wera.de/en/05060147001>

Wera - 868/4 BTZ Square-Plus  
05060147001 - 4013288041272

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**BiTorsion Bits**




Peak forces that occur in power tool applications often result in premature wear of bits or damage to the screw head. This usually occurs during initial power-up and the when the screw comes to a standstill. Screwdriving could become more productive and safer if these peak loads could be minimised. The Wera BiTorsion system prevents premature wear. The service life of the tool is extended and the productivity of power tool applications significantly increased.

**Two cushioning torsion zones**




The effectiveness of the BiTorsion system comes from a combination of two shock-absorbing spring elements. Both, bits as well as holders have a cushioning torsion zone that diverts the kinetic energy away from the drive tip during peak loads.

**BiTorsion phase 1**




The torsion spring integrated into the unique BiTorsion holder absorbs lower levels of peak loads (Phase 1). Any overloading of this spring is effectively prevented by means of a supporting mechanism.

**BiTorsion phase 2**



Higher peak loads are minimised through the torsion effect of the bit shaft (Phase 2).

**Above-average service life**



Even the service life of conventional bits is enhanced with the use of the BiTorsion holder and the BiTorsion bit also functions in a normal holder.

**Prevents premature wear**



The optimally coordinated features of the torsion zones on the bit and holder permit a phased yield when under strain. The two-phase system prevents premature wear. Moreover, a long tool service life is also ensured by the hardness of the bits that matches the respective application.

**BiTorsion and conventional tools**



The BiTorsion holder and the BiTorsion bit can, of course, be used independently of one another.

**Web link**

<https://www.wera.de/en/05060147001>

Wera - 868/4 BTZ Square-Plus  
05060147001 - 4013288041272

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Further versions in this product family:



mm



inch



mm

05060147001	#1	50	2"	4.2
05060148001	#2	50	2"	4.2
05060149001	#3	50	2"	5.5

**Web link**

<https://www.wera.de/en/05060147001>

Wera - 868/4 BTZ Square-Plus  
 05060147001 - 4013288041272

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)